

## KILN PIKA 70 L FOR CERAMIC

### TECNICAL DATA AND WARRANTY

Inside	Vol.	Width	Length	Height	Max, temp.	kW	Volt	A
Dim.	70 L	31 cm	53 cm	43 cm	1.200°C	3,6	230	20

Heaters: Kanthal AF

Thermocouple: Ni-Cr-Ni, tip K

Fuse in regulation: 0, 3 A

### **INSTRUCTION FOR MOUNTING:**

Kiln is mono phase (230 V), with regulation and safety by contactor.

The kiln must be connected with plug and protected by 20 A safety fuse.

We recommend additional ground to metal case.

### **INSTRUCTION FOR USE:**

First firing has very bad smell and smoke. We recommend making first firing in open or good ventilated place.

### **WARNING:**

Around the kiln must be clean without flammable materials as paper, plastic, etc...

Cooling hole must be about 30 cm distance from wall.

If you open the kiln in higher temperature you must be protected by gloves, spectacles and no synthetic clothes. Do not leave open door, when kilns is over 200 ° C

When you open electric cover, please disconnect electricity.

WARRANTY: 3 years, except mechanical damages.

Ljubljana, .....